


Owl 640 M

Low power, VIS-SWIR camera
640 x 512 • 15µm x 15µm pixel pitch •



Key Features and Benefits

TEC-less Visible SWIR technology

- **TEC-less Visible SWIR**
Enables ultra low power
- **15µm x 15µm pixel pitch**
Enables highest resolution VIS-SWIR image
- **Ultra high intrascene dynamic range**
Enables simultaneous capture of bright & dark portions of a scene
- **Ultra compact, Rugged, No fan**
Specially designed for integration into small OEM platforms

Resolution	640 x 512
Ultra Low Power	<2.5W
Optical Interface	C-mount
Wavelength Range	VIS-SWIR

Specification for Owl 640 M

Sensor Type	InGaAs PIN-Photodiode
Active Pixel	640 x 512
Pixel Pitch	15µm x 15µm
Active Area	9.6mm x 7.68mm
Spectral response ¹	0.6 to 1.7µm
Readout Noise (RMS) ² LG = Low Gain HG = High Gain	LG: <190e- (174e- typical) HG: <50e- (38e- typical)
Peak Quantum Efficiency	>90% @ 1.3µm
Full Well Capacity	LG: 650ke- HG: 9ke-
Pixel Operability	>99.5%
Output Format	14 bit Camera Link (base configuration)
Exposure time ³	10µs to 26.8s
Shutter mode	Global shutter
Frame Rate	Up to 120Hz
Dynamic Range (Typical)	LG: 72dB, HG: 49dB
Optical Interface	C mount
Trigger interface	Trigger IN and OUT - TTL compatible
Power supply	12V DC ±0.5V
TE Cooling	None
Image Correction	3 point NUC (offset, gain and dark current) + pixel correction
Functions controlled by serial communication	Exposure, intelligent AGC, Non-Uniformity Correction, Gamma, Pk/Av, ALC ROI
Camera Power Consumption ⁴	<2.5W (NUC ON)
Operating Case Temperature ⁵	-20°C to +55°C
Storage Temperature	-30°C to +60°C
Dimensions (L*W*H) ⁶	62.21mm x 42.00mm x 42.00mm
Weight	170g

Raptor Photonics Limited reserves the right to change this document at any time without notice and disclaims liability for editorial, pictorial or typographical errors.

Ordering Information

Camera

Owl 640 M Digital Camera	OW1.7-VS-CL-LP-640
Power Supply Cable	RPL-HR4-K

Optional Accessories

Mini PC with XCAP STD and frame grabber	RPL-PC-mf2280
Thunderbolt frame grabber	RPL-mf2280
EPIX® EB1 frame grabber	RPL-EPIX-EB1
EPIX® XCAP Std software	RPL-XCAP-STD
MDR-SDR CameraLink Cable (2m) ⁷	RPL-MCL-CBL-2M
Optical Lenses ⁸	RPL-xx-xxxx

Note 1: Optional filters available: Low, High or bandpass

Note 2: Typical readout noise is calculated from an average of the last 20 cameras shipped.

Note 3: In practice, the maximum exposure time will be dark current limited.

Note 4: Measured in an ambient of 25°C with adequate heat sinking. For full detailed power consumption values, please refer to the user manual.

Note 5: Extended operating temperature range on request.

Note 6: Dimensions include all connector parts on camera interface


Note 7: Longer Camera Link cable available.

Note 8: Please consult us to check our range of lenses

Demo is available on request.
Pricing AOR subject to volumes.

Detailed technical drawings
can be downloaded at
www.raptorphotonics.com

Quantum Efficiency



*Data supplied by sensor manufacturer

Applications

Surveillance

- 860, 1064 & 1550nm laser line detection
- Hand Held Systems
- Vision enhancement
- Machine vision
- Beam profiling

Scientific

- CubeSat / LEO applications
- Beam profiling
- Semiconductor inspection
- Solar panel cell inspection

Document #: INOWL1.7-VS-CL-LP-640 0322



Willowbank Business Park
Larne, Co Antrim
BT40 2SF,
Northern Ireland

Raptor Photonics Ltd. (UK)
T: +44(0)2828 270 141
E: sales@raptorphotonics.com
www.raptorphotonics.com

Raptor Photonics Inc. (USA)
T: +1 (877) 230-4836
E: sales@raptorphotonics.com
www.raptorphotonics.com

